


Qdos 30 Manual pump with ReNu pumphead

qdos30
Peristaltic Metering

Watson-Marlow Pumps

FEATURES AND BENEFITS

- Flow rates 0.1 ml/min (0.001 USGPH) to 500 ml/min (7.93 USGPH) at 7 bar (100psi) RMS pressure
- ReNu pumphead provides accurate, linear and repeatable flow
- Fluid recovery ensures operator safety and avoids chemical waste
- Flow control 5000:1 with $\pm 1\%$ accuracy
- 3.5" (88.9mm) colour TFT display providing pump feedback through colour, icons, graphics and text
- No valves or ancillary equipment required



Watson-Marlow... Innovation in Full Flow

PERFORMANCE

Qdos 30 pump typical flow rates

	Speed (rpm)	Flow (ml/min)*
ReNu Pumphead	0.025-125	0.1-500
	Speed (rpm)	Flow (USGPH)*
ReNu Pumphead	0.016-125	0.001-7.93


*accuracy $\pm 1\%$, repeatability $\pm 0.5\%$



Head Office | 65 -- 67 Ashwin Parade, Torrensville, South Australia, 5031
Northern Service Centre | Lot 141 Industry Drive, Whyalla Playford, 5600
ABN 24 250 583 833 | AU736-QC-HSE | ISO 9001:2008 | TQCSI QHSE:2013 | sales@asseteng.com.au

t (08) 8234 2090
f (08) 8443 4184
amepumps.com.au

Flow rate with discharge pressure for ReNu pumpheads at different drive speeds



TECHNICAL DATA

Functionality	Qdos 30 Manual
Operational modes	
Manual	•
Fluid recovery	•
Fault reporting	•
Manual control	
0.1 to 500 ml/min (5000:1)	•
Numerical flow display	•
Numerical speed display	•
Numerical percentage of max speed display	•
Fluid level monitor	•
Max (prime)	•

Functionality	Qdos 30 Manual
Security	
Auto restart	•
Fluid recovery and leak detection	•
Keypad lock	•
PIN lock to protect set up	•



ame
PUMP SPECIALISTS

t (08) 8234 2090
f (08) 8443 4184
amepumps.com.au

Head Office | 65 -- 67 Ashwin Parade, Torrensville, South Australia, 5031
Northern Service Centre | Lot 141 Industry Drive, Whyalla Playford, 5600

ABN 21 230 865 833 | AURAS QC-PSE | ISO 9001:2008 | ISO 14001:2015 | sales@assetfeng.com.au

DIMENSIONS



TECHNICAL SPECIFICATION


Ingress rating	IP66
Enclosure	Watertight / dustproof
Humidity	Non-condensing 5% to 95%
Temperature	5C to 45C (41F to 113F) Santoprene 5C to 40C (41F to 104F) SEBS
Pump weight	Drive: 4.1kg (9lb 6oz) Pumphead: 0.95kg (2lb 15oz)
Control ratio	5000:1
Noise	< 70dB(A) at 1m
Standard	CE, NSF 61, cETLus
Power supply	Switch mode power supply ~100-240V 50-60Hz 190VA

MATERIALS OF CONSTRUCTION

Component	Material
Keypad	Polyester
Drive casework	20% Glass filled PPE/ PS
Drive shaft	Stainless steel 440C
Pumphead enclosure	40% Glass filled PPS
Rotor	Glass filled nylon
Rotor bearings	Steel
Tube†	Santoprene (max 7 bar, 100 psi) SEBS (max 4 bar, 60 psi)
Hydraulic connectors	Polypropylene
Lubricant*	PFPE based (standard lubricant) Glycerol based (optional lubricant)

*The ReNu Pumphead contains lubricant. It is the user's responsibility to comply with local health and safety regulations, including ensuring chemical compatibility between the lubricant and the duty fluid before use. The standard lubricant is PFPE. A glycerol/glycol blend lubricant is also available as an option.

ORDER INFORMATION



† For guidance on chemical compatibility see www.qdospumps.com

* The pumphead side location is required when ordering. The left/right perspective assumes the user is looking at the front of the pump. The pump in the dimensions diagram is considered a pumphead located to the left.

Pumphead product codes	
Description	Partcode
ReNu pumphead 7 bar (100 psi) PFPE lubricant	0M3.2200.PFP
ReNu pumphead 7 bar (100 psi) glycerol based lubricant	0M3.2200.GLY
ReNu pumphead 4 bar (60psi) PFPE lubricant	0M3.2800.PFP

All flow rates shown were obtained pumping water at 20C (68F) with zero suction and delivery heads.
Disclaimer: The information contained in this document is believed to be correct but Watson-Marlow Limited accepts no liability for any errors it contains and reserves the right to alter specifications without notice. It is the users responsibility to ensure product suitability for use within their application. Watson-Marlow, Qdos, ReNu, LoadSure, Bioprene, Pumpsil and Marprene are trademarks of Watson-Marlow Limited. STA-PURE PFL® and STA-PURE PCS® are registered trademarks of W.L Gore & Associates Inc. Please state the product code when ordering pumps and tubing.

